

CAT. N° 0 470 23



FILTERED RECTIFIED POWER SUPPLY 1 PHASE - PRIM 230-400 V / SEC 24 V= - 120 W

Pack (number of units)	1
Volume (dm ³)	9
Weight (g)	3 705,00

Product characteristics

Single-phase power supplies

- Consisting of:
 - a safety transformer with interference filtering
 - double operating terminals
 - filter capacitors
 - fused protection in the secondary
 - a green operating voltage present indicator

24 V=

- 230-400 V ± 15 V~ (primary) / 24 V= (secondary)
- Output : 120 W
- Current : 5 A
- Terminal capacity Flexible cables Input : 6
- Terminal capacity Flexible cables Output : 6

General characteristics

Filtered rectified power supplies

- High reliability power supplies without any pollution on electrical networks
- Supplied with an insulated coupling bar for fast connection between the – and T terminals up to 15 A
- Clip-on only up to 24 W, clip-on or screw fixing up to 120 W
- Above 120 W: screw fixing
- Conform to standards IEC and EN 61558-2-6, UL 60950 and CAN/CSA-C22.2 No 60 950.00
- UL USA and Canada agreements up to 240 W
- Products suitable for building equipment conforming to standards EN 61131-2, EN 60204 and EN 60439-1

Documentation

Catalogue pages & additional information

- [Description page \(p.370\)](#)

Agreements & certificates of conformity

- [UL recogn cULus - E235045](#)

Installation instructions & related documents

- [04171402-C](#)