

Product sheet



ATLANTIC LEGRAND

Atlantic stainless steel 304L cabinet 800x600x300mm
- IP66 IK10 - 1 door

REF. 035211 | EAN. 3245060352110

> [Visit e-catalogue](#)

Product characteristics

- IP 66 according to the standard EN/IEC 60529 : completely protected against dust and against jets of water of similar force to heavy seas
- Brushed finished stainless steel. Excellent resistance to corrosion and chemical agents : 1000h resistance to salt spray
- One-piece welded body, reversible cabinet

Recommendation / Restriction

- Recommended for industrial and corrosive environments or environments that require a high level of hygiene

The product's benefits

Installation

- Double-bar lock. Equipped with universal lugs at the rear of the cabinets to facilitate the installation of accessories Autocentric of equipments

Usage

- Can be equipped with a wide range of dedicated accessories : plain or perforated plates, plinths, cable-entry plates, etc.

Documentation

TECHNICAL DOCUMENTATION

 Guide Technique : choisir son enveloppe en fonction de l'environnement | PDF (6.2Mo)

→ 041169-06.pdf | PDF (0.98Mo)

 F00095FR-14.pdf | PDF (4.44Mo)

 F00095EN--13.pdf | PDF (1.53Mo)

 Technical Guide: Choose your enclosure according to the environment | PDF (6.56Mo)

CAD & Design specs / BIM

 035211.dwg | DWG (0.05Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0419.pdf | PDF (0.06Mo)

Agreements & Certificates

 OC / CB-FR701269 | (0.39Mo)

 TUV GS-R 60175536 | (1.67Mo)

 VERITAS (BV)-03212/J0 BV | (0.59Mo)

 UL listed cULus-20150526-E164087 | (0.39Mo)

