

CAT. N° 0 676 86



## LED LAMP FOR ILLUMINATED TWO-WAY SWITCH CELIANE/MOSAIC 230 V

|                           |       |
|---------------------------|-------|
| Pack (number of units)    | 10    |
| Volume (dm <sup>3</sup> ) | 0,188 |
| Weight (g)                | 22,00 |

### Product characteristics

#### Accessories

##### Locator lights

- For illuminated function of Cat.Nos 0 770 02/12, 0 792 02/12, 0 770 32/42 and 0 792 32/42
- Connected by direct mounting
- White
- 230 V. Consumption 0.15 mA

### General characteristics

#### Mosaic™ Programme mechanisms - pushbuttons and accessories

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.506\)](#)
- [Selection chart \(p.508\)](#)
- [Selection chart \(p.512\)](#)
- [Description page \(p.877\)](#)

#### Agreements & certificates of conformity

- NF - NF012\_1596
- OC / CB - FR\_703331
- NF - 677822/A1
- OC / CB - 677823/A1
- VDE - 40044639
- OC / CB - FR\_703340
- NF - NF012\_1595

#### Installation & technical data

- [F01956EN/01](#)

#### Environmental product profile

- [Environnemental product sheet n°A E2404A-FR](#)
- [Environnemental product sheet n°A E2407A-FR](#)