

CAT. N° 0 489 17



## LIGHTING MANAGEMENT-TRAFFIC DETECTION-SURFACE MOUNTING- IR - 180°- RANGE 15 M

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,758
Weight (g)	201,00

### Product characteristics

#### Ideal for passage areas

PIR IP 42 wall/surface-mounting Lighting Management sensor, 180°

- Range 15 m
- Recommended fixing height: 2.5 m
- 3-wire with neutral
- Additional 2 A contact for HVAC control based on presence data
- Standby consumption: 0.4 W
- Can be mounted on an angle using accessory Cat.No 0 489 71

### General characteristics

#### Lighting Management sensors for 1 circuit - Lighting Management sensors for passage areas with natural light

- Check presence and natural light level continuously, switch off when there is sufficient natural light
- Occupancy mode (automatic switch-on/off factory setting)
- Can be used with push-button Cat.No 0 770 40 (or illuminated push-button Cat.No 0 770 33) for vacancy mode (manual switch-on and manual or automatic switch-off)
- Precise on-site adjustment using configuration tool Cat.No 0 882 30
- Adjustable time delay: 5 s to 59 min
- Light level threshold adjustable from 5 to 1275 lux

### Documentation

#### Catalogue pages & additional information

- [Selection chart \(p.659\)](#)
- [Description page \(p.663\)](#)
- [Motion sensors and Lighting Management sensors for controllers](#)
- [Lighting management stand-alone sensors](#)

#### Installation & technical data

- [S000077898EN-2](#)
- [LE06321AD\\_EN](#)

#### Installation instructions & related documents

- [LE06322AB](#)

#### Environmental product profile

- [Environnemental product sheet n°A E0153A-EN](#)