


Product sheet



XL³ LEGRAND

Modular distribution block with staggered bars 125 A - 15 connections per busbar - 8 modules

REF. 400403 | EAN. 3414971978485

> [Visit e-catalogue](#)

Product characteristics

- Input 10 - 35 mm² solid or 6 - 25 mm² stranded with or without ferrule
- 14 Output : 3 x 10 - 25 + 11 x 2.5 - 10 mm² rigid conductor
- 14 output : 3 x 6 - 16 + 11 x 1.5 - 10 mm² flexible conductor with or without ferrule
- In = 125A - 40°C Ui = 500 V
- Ipk = 26 kA - 60 ms Icw = 4,5 kA - 1s

The product's benefits

Installation

- Easy and fast cabling and connecting thanks to a maximised cabling space , optimized "orientation" of bars and adapted dimensions and positions of connections

Usage

- Transparent , removable and 180° rotating cover to adapt to all wiring situations

Advantages

- Maximised internal space and optimised bar orientation for easy cable access
- Connections sized and positioned to facilitate connection and answer all needs
- integrated system, to avoid accidental unscrewing of non connected screws

Documentation

TECHNICAL DOCUMENTATION

-  F03358FR-02.pdf | PDF (1.79Mo)
-  F03358EN-02.pdf | PDF (2.35Mo)

CAD & Design specs / BIM

-  400403.dwg | DWG (0.27Mo)

CATALOGUE PAGE & OTHERS

-  ex223001_0299.pdf | PDF (0.13Mo)

Agreements & Certificates

-  LGRP-01338-V01.01-EN.pdf | PDF (0.73Mo)