

# Product sheet



LEGRAND

Claws - for symmetrical rail EN 60715 - width 10 mm - for M4 screw

REF. 004416 | EAN. 3245060044169

> [Visit e-catalogue](#)

## Product characteristics

- Equipment transformers - single-phase - IP 2X or XXB up to 450 VA - up to 310 VA in 12 - 24 V - (coupling strip not mounted) - IK 04 - Clip on fixing possibility up to 160 VA with Accessories Cat.No 0 044 16 or 0 428 99 - Transformers with 2 secondary voltage supplied with coupling strip - Transformers up to 450 VA supplied with isolated strip for 0 V connection secondary / earth (except Cat.No 0 428 46) - Conform to IEC EN 61558 - 2 - 6 for 12 V, 24 V and 48 V and conform to IEC EN 61558 - 2 - 4 for 115 V and 230 V - Products suitable for building equipment conforming to standards EN 61131 - 2, EN 60204 - 1 and EN 61 439 - 1
- Accessories - For clip on rail (90° mounting) of transformers up to 160 VA with 2 claws - Claw width 10 mm - Threaded hole for M4 screw

## Documentation

### CATALOGUE PAGE & OTHERS

-  [ex223001\\_0439.pdf](#) | PDF (0.23Mo)
-  [ex223001\\_0504.pdf](#) | PDF (0.04Mo)
-  [ex223001\\_0499.pdf](#) | PDF (0.06Mo)
-  [ex223001\\_0495.pdf](#) | PDF (0.11Mo)
-  [ex223001\\_0502-0503.pdf](#) | PDF (0.06Mo)