

Product sheet



LEGRAND

Add-on modules DX³ - 3P 400 V~ - 63 A - 30 mA - A type - for 1 module DX³ MCB

REF. 410480 | EAN. 3245064104807

> [Visit e-catalogue](#)

Product characteristics

- Add - on modules DX³ - for 1 module/pole DX³ MCBs - Conform to IEC 61009 - 1, IEC 62423 (F type) - Voltage independent tripping except Cat.No 4 106 57/58/59 - AC type : detect AC components faults - A type : detect AC and DC component faults - F type (High immunity) : detect faults with AC and DC components, increased immunity to false tripping - Detection of high frequency fault currents - For mounting on the right - hand side of 1 module per pole DX³ MCBs
- 3-pole - 400 V~A Type - Sensitivity : 30 mA - Nominal rating In : 63 A - Number of modules : 3

Documentation

TECHNICAL DOCUMENTATION

 F01305FR_05.pdf | PDF (0.45Mo)

 G8191D.pdf | PDF (1.06Mo)

 F01305EN-05.pdf | PDF (0.39Mo)

CAD & Design specs / BIM

 410472.dwg | DWG (0.29Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0076-0077.pdf | PDF (0.2Mo)

 ex223001_0071.pdf | PDF (0.06Mo)

Agreements & Certificates

 OC / CB-IT-11142 | (0.36Mo)

 NF App Domestic-NF012_4423 | (0.66Mo)