

Product sheet



EMDX³ LEGRAND

EMDX3 energy meter tri 5A 230/400V RS485 2TARIFF

REF. 412041 | EAN. 3414971413733

> [Visit e-catalogue](#)

Product characteristics

- Connection with CT up to 5A.
- Communication : Modbus RS 485.
- Double tarif ; Pulse input to collect other meter (gas, water, electrical meters).
- No MID version.
- Bidirectional measure of production and consumption energies.

The product's benefits

Installation

- Easy connection of communication thanks to removable connectors. One input connector for double tariff or Pulse input to collect water or gas meters without using added concentrator device.

Usage

- Backlit display and simple access to easy reading of data. Pre-visualization of parameters. Settings mode protected by user code Bidirectional measure of production and consumption energies

Advantages

- Measure of run hours on each tariff.
- Phaseshift measure locally displayed.

Documentation

TECHNICAL DOCUMENTATION

-  F02837FR_02.pdf | PDF (4.95Mo)
-  LE11303BB_01.pdf | PDF (2.53Mo)
-  IDP000199_F02837FR_05.pdf | PDF (6.85Mo)
-  F02837EN_01.pdf | PDF (5.79Mo)
-  LE11303BA.pdf | PDF (2.5Mo)
-  PR_412041.pdf | PDF (0.33Mo)
-  IDP000367.pdf | PDF (0.32Mo)

CATALOGUE PAGE & OTHERS

-  ex223001_0120.pdf | PDF (0.06Mo)
-  ex223001_0118.pdf | PDF (0.12Mo)

 Guide Technique : EMDX³ compteurs d'énergie | PDF
(3.04Mo)

→ LE11300BD_01.pdf | PDF (0.52Mo)

 Technical Guide: EMDX³ electricity meters | PDF (3.04Mo)

 IDP000199_F02837EN_05.pdf | PDF (6.87Mo)

CAD & Design specs / BIM

 004674.dwg | DWG (0.1Mo)

Agreements & Certificates

 PEP_LGRP-01747-V01.01-EN_EMDX3.pdf | PDF (0.82Mo)