

Product sheet



EMDX³ LEGRAND

EMDX3 energy meter tri direct 63A 230/400V pulse

REF. 412090 | EAN. 3414971413870

> [Visit e-catalogue](#)

Product characteristics

- Direct connection up to 63A 3P or 3P+N.
- Communication : Pulse output.
- Pulse input to collect other meter (gas, water, electrical meters).
- No MID version.
- Bidirectional measure of production and consumption energies.

The product's benefits

Installation

- Simple installation by direct connection up to 63A without the use of a current transformer. Limited location due to its compact size of 2 modules. Easy connection of communication thanks to removable connectors. Pulse input to collect water or gas meters without using added concentrator device.

Usage

- Backlit display and simple access to easy reading of data. Pre-visualization of parameters. Settings mode protected by user code Bidirectional measure of production and consumption energies

Advantages

- Phaseshift measure locally displayed.

Documentation

TECHNICAL DOCUMENTATION

- [LE11296BD.pdf](#) | PDF (0.32Mo)
- [F02836EN_00.pdf](#) | PDF (3.78Mo)
- [IDP000195_F02836EN_04.pdf](#) | PDF (3.78Mo)
- [IDP000195_F02836_04.pdf](#) | PDF (2.1Mo)
- [EXB20065_GT_EMDX3_compteurs-energie_FR.pdf](#) | PDF (3.04Mo)
- [EXB20066_TG_EMDX3_Electricity_meters_EN.pdf](#) | PDF

CATALOGUE PAGE & OTHERS

- [ex223001_0120.pdf](#) | PDF (0.06Mo)
- [ex223001_0118.pdf](#) | PDF (0.12Mo)

(3.04Mo)

 LE11297BA.pdf | PDF (1.69Mo)

 LE11297BB.pdf | PDF (1.44Mo)

CAD & Design specs / BIM

 412090.dwg | DWG (0.11Mo)

Agreements & Certificates

 PEP_LGRP-01747-V01.01-EN_EMDX3.pdf | PDF (0.82Mo)