

Product sheet



LEGRAND

SPD - T2 - I_{max} 40 kA/pole - 3P+N - neutral on left-hand side

REF. 412245 | EAN. 3414970517722

> [Visit e-catalogue](#)

Product characteristics

- Class II (T2) low voltage SPDs - Protection against transient overvoltages for 230/400 V~ power networks (50/60 Hz). SPDs compliant with EN/IEC 61643 - 11 standards - Recommended for distribution boards
- T2 SPDs - SPDs with plug-in modules and status indicators : - Green : SPD operational - Orange : plug-in modules to be replaced
 T2 - I_{max} 40 kA/pole - SPDs recommended for power installations - Up : 1.7 kV - I_n = 20 kA/pole - U_c : 320 V~ - Earthing systems : TT, TNC, TNS - Recommended MCB : DX³ 25 A - C curve - 1P+N and 3P+N : L - N and N - PE protection modes (common and differential modes) , the N pole being protected by encapsulated spark gaps. Also called 1+1 and 3+1 - Number of poles : 3P+N - Neutral position : Left - Remote status monitoring (FS contact) : No - Number of modules : 4

Documentation

TECHNICAL DOCUMENTATION

EXB20026_TG_Surge_Protective_Devices_EN.pdf | PDF (8.37Mo)

F02060EN_05.pdf | PDF (0.62Mo)

F02060FR_06.pdf | PDF (0.61Mo)

LE07561AA_6.pdf | PDF (0.53Mo)

CAD & Design specs / BIM

412245.dwg | DWG (0.37Mo)

CATALOGUE PAGE & OTHERS

ex223001_0088-0089.pdf | PDF (0.16Mo)

ex223001_0087.pdf | PDF (0.12Mo)

ex223001_0085.pdf | PDF (0.07Mo)

Agreements & Certificates

LGRP-2015-068-V1-EN.pdf | PDF (0.62Mo)

OC / CB-AT 4283 | (0.27Mo)