

Product sheet



LCS² LEGRAND

Fixed shelf 2U for enclosures depth 115mm quick fixing

REF. 046500 | EAN. 3245060465001

Projecting mounting fixed shelf for direct screw-free fixing on 2 x 19 inches uprights. shelf is performed for a better internal ventilation, and possibility of clamping using cable ties.

> [Visit e-catalogue](#)

Description

Projecting mounting fixed shelf for direct screw-free fixing on 2 x 19 inches uprights. shelf is performed for a better internal ventilation, and possibility of clamping using cable ties.

Product characteristics

- Height 2U
- Usable width 435mm
- 1.5 mm thick steel
- 50 x 7 mm oblong perforations
- Black RAL 9005

Recommendation / Restriction

- When mounted towards the front, projecting shelves can be used as temporary work surfaces. Maximum load : 15kg

Documentation

TECHNICAL DOCUMENTATION



F01424FR-01.pdf | PDF (11.06Mo)



F01424EN-01.pdf | PDF (11.05Mo)

The product's benefits

Installation

- Automatic earthing on 19 inches uprights

CATALOGUE PAGE & OTHERS



ex223001_0952.pdf | PDF (0.16Mo)