

Product sheet



GREEN UP LEGRAND

Plastic charging station Green'up Premium 1Ph for 1 electric car - Mode 2 and 3 - Power 7,4kW 32A with DC protection

REF. 058035 | EAN. 3414972345194

> [Visit e-catalogue](#)

Product characteristics

- Local wireless communication via Bluetooth : update, configuration and control of the charging station via smartphone, tablet via App. EV charges.
- Remote IP wireless communication with the communication kit ref. 0 590 56
- External command by contactor, clock, switch (dry contact input 12 V=)
- adjustable power locally in the device or remotely through app or web pages
- Restricted access by RFID badge with the optional RFID reader ref. 0 590 59

The product's benefits

Installation

- Saves space and installation time thanks to its two sides equipped with sockets. This charging station offers the advantage of two terminals in one.

Usage

- Local wireless communication via embedded Bluetooth for configuration and control of charging station via smartphone or tablet using the IOS or Android compatible app.

Advantages

- Update of the charging station accessible easily with the Bluetooth application for the whole range. Allows you to update for free.
- Evolutive charging station using a communication kit to allow remote management such as OCPP or using RFID badge reader kit for user access management.

Documentation

TECHNICAL DOCUMENTATION

- [LE10645AA-06.pdf](#) | PDF (1.24Mo)
- [LD06264AA Stickers Charge immediate.pdf](#) | PDF (1.14Mo)
- [LE13562AA-03-LIGHT.pdf](#) | PDF (3.26Mo)
- [LE13562AA-03-FULL.pdf](#) | PDF (19.18Mo)

Software & configurators

Agreements & Certificates

-  [LGWEXFJINL](#) | (0.43Mo)
-  [OC / CB-FR_716965](#) | (0.37Mo)
-  [LGRP-01754-V01.01-FR.pdf](#) | PDF (0.97Mo)

 MODBUS TABLE GREEN-UP V1_7.zip | ZIP (0.68Mo)