

Product sheet



LIVING NOW BTICINO

Living Now - 4 ways switch, 10AX, 1 module

REF. BT-K4004 | EAN. 8005543616475

> [Visit e-catalogue](#)

Product characteristics

- The mechanism is Full - touch enhancing the ergonomics of the command : it can be operated by pressing the control at any point on its surface (above, below and in the middle)
- Full touch also means perfect flatness of the control point regardless of the load status
- Screw and plate terminals
- Easy installation and removal of the mechanism on the support frame thanks to the new generation of plastic hooking system
- 10 AX, 250 Va.c. 1P

Recommendation / Restriction

- For internal use only.

The product's benefits

Installation

- Further improvement of the installation and removal in the support frame thanks to the new generation of plastic hooks. The reduced depth of this device simplifies wall installation in case of shallow or full of cables boxes.

Usage

- Ergonomics is enhanced thanks to the new Full touch concept: the control can be operated by pressing at any point on its surface


Avantages

- The interaction is immediate and thanks to the "full touch" controls, the ergonomics of the button are completely new. In fact it can be operated in a precise way in any part thereof, at the center, top, or bottom. Once pressed, the key returns to position, remaining always perfectly aligned.
- The strength of design lies in the essentiality of the form obtained from the search for an absolute flatness between the elements of the switch.
- You can replace the device cover at any time by changing its color or restoring any damage to the surface without changing the entire device

Documentation

TECHNICAL DOCUMENTATION

CATALOGUE PAGE & OTHERS

 IDP000270_03-EN.pdf | PDF (0.11Mo)


 LE10252AC.pdf | PDF (0.68Mo)

CAD & Design specs / BIM

- BIM-BTICINO-LIVING-NOW-2025-ENGLISH.rvt | RVT (152.05Mo)
- BIM-BTICINO-LIVING-NOW-2025-FRANCAIS.rvt | RVT (69.92Mo)

 ex223001_0766.pdf | PDF (0.08Mo)

Agreements & Certificates

 AENOR-030/002588 | (0.28Mo)