

Product sheet



EMDX³ LEGRAND

EMDX3 energy meter tri direct 63A 230/400V pulse MID

REF. 412092 | EAN. 3414971413917

> [Visit e-catalogue](#)

Product characteristics

- Direct connection up to 63A 3P or 3P+N.
- Communication : Pulse output.
- Pulse input to collect other meter (gas, water, electrical meters).
- MID Certified.
- Bidirectional measure of production and consumption energies.

The product's benefits

Installation

- Simple installation by direct connection up to 63A without the use of a current transformer. Limited location due to its compact size of 2 modules. Easy connection of communication thanks to removable connectors. Pulse input to collect water or gas meters without using added concentrator device.

Usage

- Backlit display and simple access to easy reading of data. Pre-visualization of parameters. Settings mode protected by user code Bidirectional measure of production and consumption energies

Advantages

- Phaseshift measure locally displayed.

Documentation

TECHNICAL DOCUMENTATION

- IDP000196_F02840EN_04.pdf | PDF (4.16Mo)
- F02840EN_01.pdf | PDF (3.79Mo)
- IDP000196_F02840_04.pdf | PDF (1.83Mo)
- EXB20057_FR.pdf | PDF (10.47Mo)
- EXB20058_EN.pdf | PDF (10.42Mo)
- EXB20065_GT_EMDX3_compteurs-energie_FR.pdf | PDF (3.04Mo)

CATALOGUE PAGE & OTHERS

- ex223001_0120.pdf | PDF (0.06Mo)
- ex223001_0118.pdf | PDF (0.12Mo)

 EXB20066_TG_EMDX3_Electricity_meters_EN.pdf | PDF (3.04Mo)

 LE11297BA.pdf | PDF (1.69Mo)

 LE11299BD.pdf | PDF (1.77Mo)

 LE11297BB.pdf | PDF (1.44Mo)

CAD & Design specs / BIM

 412090.dwg | DWG (0.11Mo)

Agreements & Certificates

 PEP_LGRP-01747-V01.01-EN_EMDX3.pdf | PDF (0.82Mo)