

# Product sheet



## LEGRAND

Additional charger - 1000 Wfor Daker DK  
4500/6000/10000

REF. 310954 | EAN. 3245063109544




> [Visit e-catalogue](#)

## Product characteristics


- DAKER DK PLUS - On - line double conversion UPS (rack/tower) - single phase and three phase VFI - The main parameters of the UPS, including the battery charge level and faults, are displayed on the LCD screen on the front panel - The integrated communication software not only controls the UPS and its switch - off if there is a malfunction, and enables the user to test the main functions remotely, communicate via SNMP/Internet/network adaptor and access the functions of the UPS via the Internet, but can also send the user an SMS if specific events occur - The internal extension connector enables aWEB/SNMP card or a relay interface to be installed which provides insulated contacts for applications on industrial control panels or remote alarm panels - If there is an electronic fault, overload, overheating or for scheduled maintenance operations, the automatic or manual (optional) bypass ensures continuity of the power supply for critical loads. A bypass switch is available for maintenance
- Accessories - For battery cabinets Cat.Nos 3 107 44/45

## Documentation

### TECHNICAL DOCUMENTATION

-  [EXB22078\\_EN.pdf](#) | PDF (4.09Mo)
-  [EXB21082\\_EN.pdf](#) | PDF (11.02Mo)
-  [LE07976AB.pdf](#) | PDF (2.85Mo)

### CATALOGUE PAGE & OTHERS

-  [ex223001\\_0934.pdf](#) | PDF (0.08Mo)
-  [ex223001\\_0932.pdf](#) | PDF (0.09Mo)