

Product sheet



ATLANTIC LEGRAND

Atlantic stainless steel 304L cabinet 1200x800x300mm
- IP66 IK10 - 1 door

REF. 035214 | EAN. 3245060352141

> [Visit e-catalogue](#)

Product characteristics

- IP 66 according to the standard EN/IEC 60529 : completely protected against dust and against jets of water of similar force to heavy seas
- Brushed finished stainless steel. Excellent resistance to corrosion and chemical agents : 1000h resistance to salt spray
- One-piece welded body, reversible cabinet

Recommendation / Restriction

- Recommended for industrial and corrosive environments or environments that require a high level of hygiene

The product's benefits

Installation

- Double-bar lock. Equipped with universal lugs at the rear of the cabinets to facilitate the installation of accessories Autocentric of equipments

Usage

- Can be equipped with a wide range of dedicated accessories : plain or perforated plates, plinths, cable-entry plates, etc.

Documentation

TECHNICAL DOCUMENTATION

-  EXB22009_Flipbook_FR_(03_2022).pdf | PDF (6.2Mo)
-  041169-06.pdf | PDF (0.98Mo)
-  F00095FR-14.pdf | PDF (4.44Mo)
-  F00095EN--13.pdf | PDF (1.53Mo)
-  EXB22010_Flipbook_EN_(03_2022).pdf | PDF (6.56Mo)

CAD & Design specs / BIM

-  035214.dwg | DWG (0.05Mo)

CATALOGUE PAGE & OTHERS

-  ex223001_0419.pdf | PDF (0.06Mo)

Agreements & Certificates

-  TUV GS-R 60175536 | (1.67Mo)
-  VERITAS (BV)-03212/J0 BV | (0.59Mo)
-  OC / CB-FR701269 | (0.39Mo)
-  UL listed cULus-20150526-E164087 | (0.39Mo)