

Product sheet



LEGRAND

SPD - T2 - I_{max} 40 kA/pole - 440 V~ (IT) - 1P

REF. 412230 | EAN. 3414970517548

> [Visit e-catalogue](#)

Product characteristics

- Class II (T2) low voltage SPDs - Protection against transient overvoltages for 230/400 V~ power networks (50/60 Hz). SPDs compliant with EN/IEC 61643 - 11 standards - Recommended for distribution boards
- T2 SPDs - SPDs with plug-in modules and status indicators : - Green : SPD operational - Orange : plug-in modules to be replaced
- T2 - I_{max} 40 kA/pole - 440V~ (IT) - SPDs recommended for big installations - Up : 2.1 kV - I_n = 20 kA/pole - U_c : 440 V~ - Earthing systems : TT, TNC, TNS, IT - Recommended MCB : DX³ 25 A - C curve - Number of poles : 1P - Remote status monitoring (FS contact) : No - Number of modules : 1

Documentation

TECHNICAL DOCUMENTATION

-  F02060EN_05.pdf | PDF (0.62Mo)
-  F02060FR_06.pdf | PDF (0.61Mo)
-  EXB20026_TG_Surge_Protective_Devices_EN.pdf | PDF (8.37Mo)
-  LE07561AA_6.pdf | PDF (0.53Mo)

CAD & Design specs / BIM

-  412220.dwg | DWG (0.18Mo)

CATALOGUE PAGE & OTHERS

-  ex223001_0087.pdf | PDF (0.12Mo)
-  ex223001_0085.pdf | PDF (0.07Mo)
-  ex223001_0088-0089.pdf | PDF (0.16Mo)

Agreements & Certificates

-  LGRP-2015-068-V1-EN.pdf | PDF (0.62Mo)
-  OC / CB-AT 4283 | (0.27Mo)