

# Product sheet



DPX<sup>3</sup> 1600 LEGRAND

Circuit breaker DPX3 1600,3 poles, with rated current of 800A and rotary knob electronic protection unit.

REF. 422686 | EAN. 3414970767837

> [Visit e-catalogue](#)

## Product characteristics

- Breaking capacity of 100kA, according to EN/IEC standard 60947 - 2, suitable for protection of high power industrial installations. Rated insulation voltage of 1000V Rated impulse withstand voltage of 8kV
- Compliant with NEMA AB-1. Climatic condition according to IEC/EN 60947 - 1 Annex Q, Cat. F subject to temperature, humidity, vibration, shock and salt mist.
- Electronic protection unit with rotary knobs for regulation of thermal current and magnetic current. Thermal protection within range of 0,4 - 1,0 of the rated current. Magnetic protection within range of 1,5 - 10 of the rated current.
- Can be equipped with releases (undervoltage and shunt releases) and auxiliary contacts. Can be used with rotary handles or motor operator. Locking accessories are available.
- Has different type of possible connection accessories: cage terminals, spreader and rear terminals. Is available also in a plug-in version (circuit breaker fitted with special terminals and mounted on a plug-in base) or in a draw-out version (a plug-in version fitted with a "Debro-lift" mechanism which can be used to withdraw the breaker while keeping it on its base)

## The product's benefits

### Installation

- DPX3 platform has been developed to give a new solution of protection devices for a more precise approach in power installations in order to offer the correct answer for different project needs.

### Usage

- DPX3 platform provide a complete "project" approach in premium market segment, offering a range completely suitable for high power application

### Advantages

- DPX3 630 is the answer for the competition in the project sub-segment. A unique size for all versions (thermal magnetic, electronic with or without measure). Earth leakage features can be achieved by adding a dedicated module at the bottom of the breaker itself.

## Documentation

### TECHNICAL DOCUMENTATION

- [LE09131AB.pdf](#) | PDF (0.33Mo)
- [F02130FR\\_00\\_ATS\\_DPS\\_FRAv0.pdf](#) | PDF (0.29Mo)
- [EXB17039\\_GT\\_TransferSwitching.pdf](#) | PDF (17.73Mo)
- [F02130EN\\_00\\_ATS\\_DPS\\_ENGv1.pdf](#) | PDF (0.29Mo)

### CATALOGUE PAGE & OTHERS

- [ex223001\\_0223.pdf](#) | PDF (0.05Mo)
- [ex223001\\_0222.pdf](#) | PDF (0.1Mo)

