


Product sheet



LEGRAND

Add-on modules DX³ - 4P 400 V~ - 40 A - 300 mA - A type - for 1 module DX³ MCB

REF. 410528 | EAN. 3245064105286

> [Visit e-catalogue](#)

Product characteristics

- Add - on modules DX³ - for 1 module/pole DX³ MCBs - Conform to IEC 61009 - 1, IEC 62423 (F type) - Voltage independent tripping except Cat.No 4 106 57/58/59 - AC type : detect AC components faults - A type : detect AC and DC component faults - F type (High immunity) : detect faults with AC and DC components, increased immunity to false tripping - Detection of high frequency fault currents - For mounting on the right - hand side of 1 module per pole DX³ MCBs
- 4-pole - 400 V~A Type - Sensitivity : 300 mA - Nominal rating In : 40 A - Number of modules : 3

Documentation

TECHNICAL DOCUMENTATION

- [G8191D.pdf](#) | PDF (1.06Mo)
- [F01305EN-05.pdf](#) | PDF (0.39Mo)
- [F01305FR_05.pdf](#) | PDF (0.45Mo)

CAD & Design specs / BIM

- [410500.dwg](#) | DWG (0.29Mo)

CATALOGUE PAGE & OTHERS

- [ex223001_0076-0077.pdf](#) | PDF (0.2Mo)
- [ex223001_0071.pdf](#) | PDF (0.06Mo)

Agreements & Certificates

- [NF-NF012_1340](#) | (0.79Mo)
- [LGRP-00802-V01.01-EN.pdf](#) | PDF (0.64Mo)
- [OC / CB-IT-11142](#) | (0.36Mo)