

CAT. N° 0 260 88



RESIDUAL CURRENT RELAY - TO CLIP ON RAIL - 2 MODULES

Pack (number of units)	1
Volume (dm ³)	0,354
Weight (g)	201,00

Product characteristics

Residual current relay

- Detects fault currents, and, when used with a shunt trip or an undervoltage release, it gives the trip command to a MCCB or a switch
- Comprises:
 - a tinged, sealable window
 - an auxiliary contact
 - a green Led indicating energisation
 - 3 yellow Leds indicating respectively the max. phase earth insulation current: 20, 40 and 60 %
 - a red Led indicating
- Fixed: exceeding of the insulation fault current value
- Flashing: breaking of one of the connections between coils and relays
- For use with coils:
 - Ø35 and 80 mm with adjustable sensitivity: 0.03, 0.05, 0.075, 0.1, 0.15, 0.2, 0.3, 0.5, 0.75, 1, 1.5, 2, 3, 5, 7.5, 10, 15, 20, 30 A
 - Ø110 to 210 mm with adjustable sensitivity: 0.3, 0.5, 0.75, 1, 1.5, 2, 3, 5, 7.5, 10, 15, 20, 30 A
 - Ø150 mm with adjustable sensitivity: 0.5, 0.75, 1, 1.5, 2, 3, 5, 7.5, 10, 15, 20, 30 A
 - Ø300 mm with adjustable sensitivity: 1, 1.5, 2, 3, 5, 7.5, 10, 15, 20, 30 A
- Adjustable trip: 0, 0.15, 0.25, 0.5, 1, 2.5, 5 seconds
- Supply voltage: 230/240 V - 50/60 Hz
- Residual current relay to clip on symmetrical rail
- Number of modules : 2

General characteristics

Residual current relay and coils

- Add residual current protection to DPX³ trip-free switches and DPX³ MCCBs equipped with release

Documentation



Catalogue pages & additional information

- [Description page \(p.155\)](#)



Installation instructions & related documents

- [F3664D](#)