

CAT. N° 0 427 62



## SAFETY TRANSFORMER 230 V / 12 V - 160 VA - 2 X 4 MM<sup>2</sup>

Pack (number of units)	1
Volume (dm <sup>3</sup> )	6
Weight (g)	4 005,00

### Product characteristics

#### Safety transformers

- Conform to standard IEC EN 61558-2-6
- For 63 VA transformers:
  - Fuse cartridges: 5 x 20 time-delayed
  - Fuse carrier: Cat.No 0 371 81
- For 100 VA and greater transformers:
  - Up to 25 A : gG 10 x 38 fuse cartridges and fuse carrier Cat. No. 0 058 08
  - From 25 A to 50 A : gG 14 x 51 fuse cartridges and fuse carrier Cat.No 0 215 01
  - From 50 A upwards : gG 22 x 58 fuse cartridges and fuse carrier Cat.No 0 216 01
  - C curve MCBs

**Input voltage = 230 V~ Output voltage = 12 V~**

- Power : 160 VA
- Primary terminal flexible cable : 4 mm<sup>2</sup>
- Secondary terminal flexible cable cross-section : 4 mm<sup>2</sup>

### General characteristics

**Transformers and auto-transformers IP 55 - class II - single-phase**

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.362\)](#)
- [Technical page \(p.366\)](#)
- [Technical page \(p.367\)](#)
- [Protection of transformers and their lines](#)