

CAT. N° 0 770 15


ENERGY SAVING SWITCH MOSAIC - 10 AX 250 V~ - WHITE

Pack (number of units)	1
Volume (dm ³)	0,235
Weight (g)	61,00

Product characteristics
Switches 10 AX - 250 V~
Energy saving switches

- Automatic terminals
- Are installed and work like conventional 2-way switches. In addition, they automatically switch off after 10 mins if no movement is detected by the built-in IR detection cell
- Detection field: 160°. Detection range: 8 m
- Compatible with any lamp:
 - 12-150 W: incandescent and 230 V halogen lamps
 - 12-150 VA: lamps with electronic or ferromagnetic ballast
 - 8-30 W (or 650 mA): LED and CFL
- All types of lamps can be mixed on the same circuit
- Ideal for rooms where the light may be left switched on needlessly (child's bedroom, box room)
- White

General characteristics
Mosaic™ Programme mechanisms - switches

- All two-way switches with indicator have a terminal for neutral connection and have to be equipped with an indicator

Documentation

Catalogue pages & additional information

- [Description page \(p.876\)](#)
- [Technical page \(p.882\)](#)


Installation & technical data

- [F01916EN-04](#)