

CAT. N° 0 427 63



SAFETY TRANSFORMER 230 V / 12 V 250 VA - 2 X 4 MM²

Pack (number of units)	1
Volume (dm ³)	6
Weight (g)	6 435,00

Product characteristics

Safety transformers

- Conform to standard IEC EN 61558-2-6
- For 63 VA transformers:
 - Fuse cartridges: 5 x 20 time-delayed
 - Fuse carrier: Cat.No 0 371 81
- For 100 VA and greater transformers:
 - Up to 25 A : gG 10 x 38 fuse cartridges and fuse carrier Cat. No. 0 058 08
 - From 25 A to 50 A : gG 14 x 51 fuse cartridges and fuse carrier Cat.No 0 215 01
 - From 50 A upwards : gG 22 x 58 fuse cartridges and fuse carrier Cat.No 0 216 01
 - C curve MCBs

Input voltage = 230 V~ Output voltage = 12 V~

- Power : 250 VA
- Primary terminal flexible cable : 4 mm²
- Secondary terminal flexible cable cross-section : 4 mm²

General characteristics

Transformers and auto-transformers IP 55 - class II - single-phase

Documentation

Catalogue pages & additional information

- [Description page \(p.362\)](#)
- [Technical page \(p.366\)](#)
- [Technical page \(p.367\)](#)
- [Protection of transformers and their lines](#)