

CAT. N° 1 467 01



## SINGLE-PHASE SWITCHING MODULES POWER SUPPLY - 12 W - INPUT 100-240 V~ / OUTPUT 5 V=

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,167
Weight (g)	88,00

### Product characteristics

#### Single-phase - 12 - 92 W

- No-load power consumption
- Adjustable output voltage

#### Input voltage: 100 to 240 V~ Output voltage: 5 V=

- Nominal power : 12 W
- Rated current : 2.4 A
- Setting range : 4.5 to 5.5 V
- Number of modules : 1

### General characteristics

#### Switching mode power supplies - single-phase

- Conform to standards UL 508, UL 60950, EN 61558-2-16 and IEC EN 60950-1, EN 55022 class B, EN 61000-3-2, EN 61000-3-3, EN 61000-6-2 and EN 61204-3
- Operating frequency: 50/60 Hz
- Output voltage present indicator
- Output voltage adjustment potentiometer on front panel
- Integrated short-circuit and overload protection
- For mounting on a symmetrical rail depth 7.5 mm and 15 mm

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.097\)](#)
- [Dimensions of din-rail equipment](#)

#### Installation & technical data

- [F02467EN-01](#)

#### Installation instructions & related documents

- [LE09915AA-00](#)

#### Agreements & certificates of conformity

- [UL listed cULus - E223674](#)