

CAT. N° 0 784 58



180° MOTION SENSOR -IP40 -8 M -FLUSH-MOUNTING -WITHOUT OVERRIDE -PIR -CARDBOARD

Pack (number of units)	1
Volume (dm ³)	0,235
Weight (g)	93,00

Product characteristics

2-wire motion sensors, without neutral

- IR detection
- Accepted power by lamp type:
 - LEDs: 3 to 100 W
 - compact fluorescent: 3 to 100 W
 - LEDs, CFLs, Halogen, fluo tubes with ferromagnetic or electronic transformer: 3 to 250 VA
 - halogen 230 V, incandescent: 3 to 250 W
- For LED and compact fluorescent lamps
- If several sensors are installed on the same circuit, the minimum load changes: refer to the technical sheet
- Possibility to install up to 3 sensors in parallel
- Time delay setting from 10 s to 10 min
- Light level threshold setting from 5 lux to 1275 lux
- Standby consumption : 0.2 W

Sensor without override

- Cardboard
- Range 8 m
- Recommended fixing height: 1.2 m
- 2-wire without neutral
- Light level threshold: 5 to 1275 lux
- Adjustable time delay: 10 s to 10 min
- Standby consumption: 0.2 W

General characteristics

Mosaic™ Programme mechanisms - motion and presence sensors

- All sensors are compatible with any lamp - Detection field: 120°
- Detection range: 8 m
- Recommended installation height: 1.20 m
- Integrated self-protection against overloads and short-circuits.
- 2 modules

Documentation

Catalogue pages & additional information

- [Selection chart \(p.658\)](#)
- [Selection chart \(p.659\)](#)
- [Description page \(p.661\)](#)
- [Technical page \(p.662\)](#)
- [Description page \(p.880\)](#)
- [Technical page \(p.882\)](#)
- [Motion sensors and Lighting Management sensors for controllers](#)

Installation & technical data

- F01983EN-03

Installation instructions & related documents

- [LE08095AD](#)