

CAT. N° 0 904 72



SURFACE MOUNTING SOCKET GREEN'UP ACCESS - IP66- IK08 - GERMAN STANDARD

Pack (number of units)	1
Volume (dm ³)	4,047
Weight (g)	470,00

Product characteristics

Mode 1 and Mode 2 sockets - 16 A EV

- Heavy-duty mechanisms with silvered contacts
- Single-phase sockets - screw connection - 230 V
- Supplied with base Cat.No 0 904 78 for hanging up the vehicle charging cable control box
- For charging 1 vehicle
- Conform to IEC 60-884-1

IP 55 - IK 08 surface-mounting

- Suitable for installation in private houses
- Plastic socket with flap cover
- Supplied complete with surface mounting box fitted with an ISO 20 cable gland
- Dimensions (H x W x D): 98 x 98 x 70 mm (exc. cable gland)
- German standard socket outlet

General characteristics

Green'up™ Access sockets 16 A - 230 V - 16 A EV - for electric vehicles

- Used for safely charging rechargeable electric and hybrid vehicles which take Mode 2 cord (compatible with Mode 1)
- Connected to the consumer panel via one 3 x 2.5 mm² dedicated line (1 line per socket) protected by 30 mA - 20 A C curve, type A or Hpi RCBO (or 30 mA type A or HPi RCCB + 20 A C curve circuit breaker)
- Recommended installation height: 1.30 m from the floor
- Suitable for residential and workplace use

Documentation

Catalogue pages & additional information

- [Selection chart \(p.372\)](#)
- [Description page \(p.373\)](#)
- [Technical page \(p.376\)](#)

Installation & technical data

- [F01850EN-04](#)

Installation instructions & related documents

- [LE05012AF](#)

Agreements & certificates of conformity

- [MEEI-UP 69253203 0001](#)
- [OC / CB-HU-001641](#)