

CAT. N° 1 467 23



SINGLE-PHASE SWITCHING MODULES POWER SUPPLY - 60 W - INPUT 100-240 V~ / OUTPUT 24 V=

Pack (number of units)	1
Volume (dm ³)	0,363
Weight (g)	217,00

Product characteristics

Single-phase - 12 - 92 W

- No-load power consumption
- Adjustable output voltage

Input voltage: 100 to 240 V~ Output voltage: 24 V=

- Double output terminal block
- Nominal power : 60 W
- Rated current : 2.5 A
- Setting range : 21.6 to 29 V
- Number of modules : 3

General characteristics

Switching mode power supplies - single-phase

- Conform to standards UL 508, UL 60950, EN 61558-2-16 and IEC EN 60950-1, EN 55022 class B, EN 61000-3-2, EN 61000-3-3, EN 61000-6-2 and EN 61204-3
- Operating frequency: 50/60 Hz
- Output voltage present indicator
- Output voltage adjustment potentiometer on front panel
- Integrated short-circuit and overload protection
- For mounting on a symmetrical rail depth 7.5 mm and 15 mm

Documentation

Catalogue pages & additional information

- [Description page \(p.097\)](#)
- [Dimensions of din-rail equipment](#)

Installation & technical data

- [F02467EN-01](#)

Installation instructions & related documents

- [LE09915AA-00](#)

Agreements & certificates of conformity

- [UL listed cULus - E223674](#)