

CAT. N° 3 101 77



DAKER DK PLUS CONVERTIBLE UPS WITHOUT BATTERY - SINGLE PHASE VFI - 10000 VA - 10000 W

Pack (number of units)	1
Volume (dm ³)	138,459
Weight (g)	22 800,00

Product characteristics

Convertible UPS without batteries

Single phase

- Nominal power: : 10000 VA
- Active power: : 10000 W
- Phase configuration: : none
- Weight: : 26 kg

General characteristics

DAKER DK PLUS - On-line double conversion UPS (rack/tower) - single phase and three phase VFI

- The main parameters of the UPS, including the battery charge level and faults, are displayed on the LCD screen on the front panel
- The integrated communication software not only controls the UPS and its switch-off if there is a malfunction, and enables the user to test the main functions remotely, communicate via SNMP/Internet/network adaptor and access the functions of the UPS via the Internet, but can also send the user an SMS if specific events occur
- The internal extension connector enables aWEB/SNMP card or a relay interface to be installed which provides insulated contacts for applications on industrial control panels or remote alarm panels
- If there is an electronic fault, overload, overheating or for scheduled maintenance operations, the automatic or manual (optional) bypass ensures continuity of the power supply for critical loads. A bypass switch is available for maintenance

Documentation

Catalogue pages & additional information

- [Description page \(p.707\)](#)
- [Technical page \(p.708\)](#)
- [DAKER DK PLUS](#)

Environmental product profile

- [LGRP-00428-V02](#)

Installation & technical data

- [UPS_LGR_0110_GB_AA](#)