

CAT. N° 1 466 03



## STABILISED SWITCHED MODULES POWER SUPPLY - SINGLE-PHASE - 20-60 W-OUTPUT 12 V= -60 W

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,566
Weight (g)	302,00

### Product characteristics

#### Single-phase 20 - 60 W

- No-load power consumption
- Adjustable output voltage
- Plastic casing

#### Input voltage: 100 to 240 V~ Output voltage: 12 V=

- Nominal power : 60 W
- Nominal rating : 5.00 A
- Setting range : 12 to 15 V
- Width : 40 mm

### General characteristics

#### Stabilised switched mode power supplies - single-phase

- Conforming to standards UL 508, IEC EN 60950-1 and IEC EN 61204-3
- UL-approved in USA and Canada
- Operating frequency: 50/60 Hz
- Output voltage present indicator
- Potentiometer for adjusting the output voltage on front panel
- With signal or relay contact for feedback on the status of the active output voltage (except 75 W)
- Connection with copper conductors only
- For mounting on a symmetrical rail depth 7.5 mm and 15 mm

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.368\)](#)
- [Stabilised switched mode power supplies](#)

#### Installation & technical data

- [F02123EN-00](#)

#### Installation instructions & related documents

- [LE07893AA](#)

#### Agreements & certificates of conformity

- [UL listed cULus - E223674](#)