

CAT. N° 4 102 02


MCB - DX³ - 50 KA - 2P - 230/400 V~ - 25 A - D CURVE

Pack (number of units)	1
Volume (dm ³)	0,605
Weight (g)	458,00

Product characteristics
2-pole - 230/400 V~

- D curve
- Nominal rating I_n : 25 A
- Number of modules : 3

General characteristics
MCBs DX³ - 50 kA - thermal magnetic MCBs from 10 A to 63 A - C and D curves

- Breaking capacity:
 - 50 kA - IEC 60947-2 - 400 V~
 - Can be equipped with DX³ auxiliaries and accessories

Documentation
 **Catalogue pages & additional information**

- [Description page \(p.069\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)

 **Installation & technical data**

- [F01220EN-01](#)

 **Installation instructions & related documents**

- [LE03603AG](#)

 **Environmental product profile**

- [Environnemental product sheet n°8 E0084A-FR](#)
- [LGRP-00269-V01](#)