

CAT. N° 4 120 90



THREE-PHASE METER EMDX³ WITH DIRECT CONNECTION - NON-MID - 63 A - PULSE OUTPUTS - 4 MODULES

Pack (number of units)	1
Volume (dm ³)	0,57
Weight (g)	245,00

Product characteristics

Three-phase meters

Direct connection

- One pulse type input for other types of meters (gas, water, etc.)
- Non-MID :
- Maximum current : 63 A
- Output type : Pulse
- Dual tariff : No
- Number of modules : 4

General characteristics

EMDX³ electrical energy meters - rail mounting

- Measure the electricity consumed by a single-phase or three-phase circuit downstream of the electricity distribution metering
- Display electricity consumption in kWh, as well as other values such as current, active energy, reactive energy and power (depending on the catalogue number)
- Conform to standards IEC 61557-12, IEC 62053-21/23, IEC 62052-11 and IEC 62052-31
- MID compliance ensures accuracy of the metering with a view to recharging for the electricity used

Documentation

Catalogue pages & additional information

- [Description page \(p.102\)](#)
- [Technical page \(p.107\)](#)

Installation & technical data

- [F02836EN_00](#)
- [IDP000195_F02836EN_04](#)
- [LE11297BA](#)

Installation instructions & related documents

- [LE11296BD](#)
- [LE11297BB](#)