

CAT. N° 4 149 18



## MEASUREMENT MODULE CX<sup>3</sup> - DIRECT CONNECTION UP TO 63A - 3 X SINGLE-PHASE + 3 COILS - 1 MODULE

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,332
Weight (g)	115,00

### Product characteristics

#### Measurement modules

- For measuring current, voltage, active/reactive power and other values
- Conform to IEC/EN 61557-12
- Accuracy: class 0.5

#### Direct connection up to 63 A with closed Rogowski coils

- Allow the passage of prong-type supply busbars (upper side)
- Supplied with closed Rogowski coils
- 3 x single-phase measuring module + 3 coils
- Consumption: 0,418 W - 34,8 mA (12 V =)
- Number of modules : 1

### General characteristics

#### CX<sup>3</sup> energy management system

- Conform to IEC/EN 61131-2 (Programmable controllers)
- CX<sup>3</sup> energy management system enables to measure, control and visualize the state of rail mounting protection devices (MCBs, RCCBs, RCBOs, etc...) and head equipment (DMX<sup>3</sup> and DPX<sup>3</sup>), locally ("Stand alone" ) or remotely
- All the modules of the system are equipped with two specific communication ports: one at the backside (for communication rail) and one underneath (for communication patch cords)
- Power supply with specific module Cat.No 4 149 45
- Remote configuration possible with the help of the Energy Management Configuration Software, available for free download via E-Catalogue (giving also access to a 30-day trial version of Energy Management Software Cat.No 4 149 38/39)

### Documentation

#### Installation instructions & related documents

- [LE08380AC](#)

#### Installation & technical data

- [F02335EN-03](#)
- [ModbusTable\\_EMS\\_414918\\_3x1PN\\_v1](#)