

CAT. N° 4 149 32



UNIVERSAL CONTROL MODULES CX³ - 2 RELAYS 240 V~ - 6 A - 1 MODULE

Pack (number of units)	1
Volume (dm ³)	0,219
Weight (g)	62,00

Product characteristics

Universal control module

- Enables upstream busbar connection
- 2 relays: 240 V~ - 6 A
- Enables to remotely control different electrical loads or motorised controls associated to symmetrical rail mounting protection devices or head equipment (DPX³ MCCBs)
- Equipped with DIP switches (on the side) allowing product configuration: contact type (NO + NC, 2 NO, etc...) and function (maintained or momentary contact)
- Consumption: 0.456 W - 38 mA (12 V =)
- Number of modules : 1

General characteristics

CX³ energy management system

- Conform to IEC/EN 61131-2 (Programmable controllers)
- CX³ energy management system enables to measure, control and visualize the state of rail mounting protection devices (MCBs, RCCBs, RCBOs, etc...) and head equipment (DMX³ and DPX³), locally ("Stand alone") or remotely
- All the modules of the system are equipped with two specific communication ports: one at the backside (for communication rail) and one underneath (for communication patch cords)
- Power supply with specific module Cat.No 4 149 45
- Remote configuration possible with the help of the Energy Management Configuration Software, available for free download via E-Catalogue (giving also access to a 30-day trial version of Energy Management Software Cat.No 4 149 38/39)

Documentation

Catalogue pages & additional information

- [Description page \(p.100\)](#)

Installation & technical data

- [F02333EN-02](#)
- [ModbusTable_EMS_414932_Breaker_v1](#)
- [ModbusTable_EMS_414932_Contactor_v1](#)
- [ModbusTable_EMS_414932_Generic_v1](#)
- [Instal-Manual-RA00163AB-EN](#)
- [MODBUS TABLE EMS 414932 Command Breaker](#)
- [MODBUS TABLE EMS 414932 Command GenericOutput](#)

Installation instructions & related documents

- [LE08383AC](#)

Softwares

- [Legrand Energy Management Software](#)