

CAT. N° 4 122 72



SPD - PROTECTION OF MAIN DISTRIBUTION BOARD - T1+T2 - LIMP 12.5 KA/POLE - 3P

Pack (number of units)	1
Volume (dm ³)	0,521
Weight (g)	451,00

Product characteristics

SPDs for general protection of main distribution board

- SPDs with plug-in modules and status indicators:
 - Green: SPD operational
 - Orange: plug-in modules to be replaced
- Earthing systems: TT, TNC, TNS

T1+T2 - limp 12,5 kA/pole

- For general protection of big installations and protection of small installations with external lightning protection (LPS).
- Up: 1.5 kV - I_{max}: 60 kA/pole - U_c: 320 V-
- Recommended MCB: DX³ 63 A - C curve
- Number of poles : 3P
- I_{total} (10/350) : 37.5 kA
- Remote status monitoring (FS contact) : Yes
- Number of modules : 3

General characteristics

Class I + II (T1+T2) low voltage SPDs

- Protection against transient overvoltages for 230/400 V-power networks (50/60 Hz).
- SPDs compliant with EN/IEC 61643-11 standards
- Recommended for main distribution boards
- Class I+II (T1+T2) : SPDs tested and specified according to both T1 and T2 test classes

Documentation



Catalogue pages & additional information

- [Technical page \(p.074-075\)](#)
- [Description page \(p.076\)](#)
- [Technical page \(p.079\)](#)
- [Technical page \(p.080-081\)](#)
- [Dimensions of din-rail equipment](#)



Installation & technical data

- [F02060EN_05](#)



Installation instructions & related documents

- [LE07561AA_6](#)