

CAT. N° 5 740 97



AUTOMATIC SWITCH ARTEOR - WITH NEUTRAL - 3-WIRE - 1000 W- 2 MODULES - MAGNESIUM

Pack (number of units)	1
Volume (dm ³)	0,237
Weight (g)	73,00

Product characteristics

Motion sensors

- Measurement of luminosity threshold
- Adjustment of luminosity threshold and time delay
- Max. lux and min. time delay factory pre-set
- Recommended fixing height: 1 m
- IR detection 180°
- Adjustable luminosity threshold: 5 to 1275 lux
- Installation in box min. depth 40 mm recommended
- 2 modules
- Range 8 m

With neutral, 3-wire - 2000 W

- Operates:
 - 2000 W incandescent and halogen lamps 230 V~
 - 1000 VA ELV halogen lamps with ferromagnetic or electronic transformer
 - 500 VA compact fluorescent lamps
 - 0 to 250 W for LEDs
- Settings modified on the device via thumbwheel or configuration tool
Cat.Nos 0 882 30 and 0 882 35
- Time delay adjustable from 5 s to 30 min
- Magnesium

General characteristics

Arteor™ motion sensors

- Mechanisms supplied with rocker plates, to be equipped with support frames and plates

Documentation

Catalogue pages & additional information

- [Description page \(p.455\)](#)
- [Technical page \(p.457\)](#)

Installation & technical data

- S000074408EN-05

Installation instructions & related documents

- [LE05025AC](#)

Agreements & certificates of conformity

- [OC / CB-645761A](#)