

CAT. N° 6 054 70



XL³-N 250 DISTRIBUTION BOARD - SURFACE MOUNTING - 12 POLES - MAX. 125 A

Pack (number of units)	O/R
Volume (dm ³)	O/R
Weight (g)	O/R

Product characteristics

XL³-N 250 distribution boards

Maximum rating 125 A

- To be equipped with mounting kit for main circuit breaker (DIN-rail mounting MCBs or DRX 125 or DPX³ 160 MCCBs)
- Surface mounting
- Number of poles : 12 outgoing terminals
- No of 3P ways : 4

General characteristics

XL³-N 250 3-phase distribution boards - from 12 to 54 poles (outgoing terminals)

- 3-phase distribution boards for DIN-rail mounting circuit breakers; IP 40 (IP 41 with the kit Cat.No 6 027 98) - IK 08 with door
- Conform to standard IEC 61439-2; Type tested; tested and certified by third part laboratory
- Maximum voltage 480 V~; Rated short-time withstand current (I_{cw}): 17 kA 0.2 s; Rated peak withstand current (I_{pk}): 34 kA
- Ambient temperature: 50 °C continuously
- Zinc coated metal; Grey RAL 7035
- Supplied with: surface or flush-mounting box, reversible door with handle, faceplate, fully isolated tin plated copper busbar
- The number of holes of earth and neutral terminal blocks are equal to the number of outgoing devices

Documentation

Catalogue pages & additional information

- [Description page \(p.210\)](#)
- [Technical page \(p.211\)](#)

Installation & technical data

- [F02537EN-01](#)