

CAT. N° 4 159 57



**DX<sup>3</sup> STOP ARC 10000 WITH BOTTOM SIDE SUPPLY - 1P+N ON RIGHT-HAND SIDE - 30 MA - A TYPE 230 V~ - 13 A - 3 MODULES -B CURVE**

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,521
Weight (g)	331,00

**Product characteristics**

**Arc fault detection residual current circuit breakers**

- Breaking capacity:
  - 10000 - IEC 61009-1 - 230/240 V~
  - Compatible with both prong-type and fork type supply busbars

**Single pole + neutral 230 V~ A Type 30 mA**

- Neutral on right-hand side
- B curve
- Nominal rating I<sub>n</sub> : 13 A
- Number of modules : 3

**General characteristics**

**DX<sup>3</sup> Stop Arc - bottom side supply - arc fault detection devices from 10 to 20 A**

- Conform to IEC/EN 62606
- Can be equipped with DX<sup>3</sup> signalling and remote tripping auxiliaries
- Specific use: fire prevention by arc detection

**Documentation**

 **Video**


- [DX3-StopArc\\_EN\\_N\\_RIGHT](#)

 **Installation instructions & related documents**

- [LE10543AA](#)

 **Documents & videos**

- [DX3-StopArc\\_EN\\_N\\_RIGHT](#)

 **Catalogue pages & additional information**

- [Description page \(p.063\)](#)
- [Dimensions of din-rail equipment](#)
- [Performance of MCBs and auxiliaries](#)

 **Installation & technical data**

- [F02546EN-03](#)