

CAT. N° 7 530 52



STAR ARCHITECTURE TV-R-SAT SOCKET VALENA IN'MATIC

Pack (number of units)	5
Volume (dm ³)	1,912
Weight (g)	594,00

Product characteristics

Star architecture TV sockets

- For DVBT, Cablecast and satellite installation. UHD TV compatible. Class A shielded star socket LTE Ready (4G protected)
- Recommended coaxial cable: 17 VATC. Star cabling (1 socket = 1 cable to antenna, splitter or multiswitch)
- Visual check of the connection
- Meet EN 50083-4 and EN 50083-2 European directive
- Star cabling (1 socket = 1 cable to antenna) ensures a HD quality level of distribution of TV standard
- For distribution of TV and Radio signals. All operators (DVBT, satellite, Cablecast)
- Meet EN 50083-4 and CEM 50083-2 European Directive. HDTV compatible: Low fading (less than 1.5 dB)
- LTE ready, shielded socket to protect against interference from mobile phone network 3G and 4G signals
- TV male connector (Ø9.5 mm): 5-68/120-862 MHz less than 1.5 dB. R female connector (Ø9.5 mm): 87.5 - 108 MHz less than 1.5 dB. SAT "F" type connector: 950-2400 MHz

TV-R-SAT socket

- Low attenuation: 1.5 dB
- TV: 5768/120?862 MHz
- R: 87.5 ? 108 MHz
- SAT: 950?2400 MHz

General characteristics

Valena™ IN'MATIC mechanisms - TV sockets

- Valena In'Matic mechanisms are supplied with metal support, for claw or screw mounting
- To be equipped with Valena Life or Valena Allure cover plates and plates
- Supplied with mounted dust protection transparent shield
- Packaged in boxes

Documentation



Catalogue pages & additional information

- [Description page \(p.499\)](#)
- [Selection chart \(p.509\)](#)
- [Selection chart \(p.513\)](#)
- [Valena, Synergy and MosaicTMProgramme - TV sockets](#)



Installation & technical data

- [F02112EN-01](#)



Installation instructions & related documents

- [LE07425CD](#)