

CAT. N° 8 332 85



BRITISH STANDARD RCD SYNERGY -ELO DOUBLE POLE 30 MA 1 GANG -13 A -250 V~ -AUTHENTIC POLISHED STAINLESS STEEL

Pack (number of units)	O/R
Volume (dm ³)	O/R
Weight (g)	O/R

Product characteristics

RCD sockets 13 A - 250 V~

- Conform to BS 7288: 1990 and BS 1363 - Part 2: 1995
- Conventional earth pin release shutter
- Maximum operating current 16 A
- Electronic RCD module with a membrane switch for "test and reset"
- Flush mounting back box : min. 25 mm deep

ELO - DP 30 mA - 1 gang

- Trips in the event of a power failure
- Ideal for applications where it is desirable to prevent automatic reactivation of equipment after a power failure
- For hazardous, e.g. machinery, power tools
- Nominal plate dimensions: 86 x 86 mm
- Polished stainless steel

General characteristics

Synergy™ - British standard RCD sockets - Authentic

- Slim front plate:
 - BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
 - PSS: Plates made of Stainless Steel + rust resistance
 - GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

Documentation



Catalogue pages & additional information

- [Description page \(p.588\)](#)



Installation instructions & related documents

- [LE08955AA](#)