

CAT. N° 6 054 71



## XL<sup>3</sup>-N 250 DISTRIBUTION BOARD - SURFACE MOUNTING - 18 POLES - MAX. 125 A

Pack (number of units)	O/R
Volume (dm <sup>3</sup> )	O/R
Weight (g)	O/R

### Product characteristics

#### XL<sup>3</sup>-N 250 distribution boards

##### Maximum rating 125 A

- To be equipped with mounting kit for main circuit breaker (DIN-rail mounting MCBs or DRX 125 or DPX<sup>3</sup> 160 MCCBs)
- Surface mounting
- Number of poles : 18 outgoing terminals
- No of 3P ways : 6

### General characteristics

#### XL<sup>3</sup>-N 250 3-phase distribution boards - from 12 to 54 poles (outgoing terminals)

- 3-phase distribution boards for DIN-rail mounting circuit breakers; IP 40 (IP 41 with the kit Cat.No 6 027 98) - IK 08 with door
- Conform to standard IEC 61439-2; Type tested; tested and certified by third part laboratory
- Maximum voltage 480 V~; Rated short-time withstand current (I<sub>cw</sub>): 17 kA 0.2 s; Rated peak withstand current (I<sub>pk</sub>): 34 kA
- Ambient temperature: 50 °C continuously
- Zinc coated metal; Grey RAL 7035
- Supplied with: surface or flush-mounting box, reversible door with handle, faceplate, fully isolated tin plated copper busbar
- The number of holes of earth and neutral terminal blocks are equal to the number of outgoing devices

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.210\)](#)
- [Technical page \(p.211\)](#)

#### Installation & technical data

- [F02537EN-01](#)