


CAT. N° 6 510 40



## FLEXIBLE CONDUIT - MEDIUM IMPACT - SHOCK RESISTANCE 2 JOULES - Ø EXT. 40 MM

Pack (number of metres)	50
Volume (dm <sup>3</sup> )	135,2
Weight (g)	7 817,00

### Product characteristics

#### Medium impact (ICA 3321)

- Material: PVC without Pb, Sn, Cd (RoHS compliant)
- Light grey (RAL 7035)
- Impact resistance: 2 joules at - 5 °C
- Min operating t°: - 5 °C
- Max operating t°: + 60 °C
- IK 07
- Flush-mounted in certain cases before construction of the masonry
- Ø exterior: : 40 mm
- Ø interior: : 31.2 mm
- colour of ties on coil: : white

### General characteristics

#### Flexible conduits

- Non flame propagating
- Conform to standard EN/IEC 61386-22
- Crush resistance: 750 Newtons
- Supplied wrapped in film, the coil acts as a pay-out reel
- The various diameters are identified by coloured ties
- Surface-mounting or flush-mounting

### Documentation



#### Catalogue pages & additional information

- [Description page \(p.619\)](#)
- [Flexible conduits](#)



#### Agreements & certificates of conformity

- [NF 004 - 60050610C1](#)