

CAT. N° 8 330 85

**BRITISH STANDARD RCD SYNERGY -ELO DOUBLE POLE  
30 MA 1 GANG -13 A -250 V~ -AUTHENTIC BRUSHED  
STAINLESS STEEL**

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,462
Weight (g)	208,00

**Product characteristics****RCD sockets 13 A - 250 V~**

- Conform to BS 7288: 1990 and BS 1363 - Part 2: 1995
- Conventional earth pin release shutter
- Maximum operating current 16 A
- Electronic RCD module with a membrane switch for "test and reset"
- Flush mounting back box : min. 25 mm deep

**ELO - DP 30 mA - 1 gang**

- Trips in the event of a power failure
- Ideal for applications where it is desirable to prevent automatic reactivation of equipment after a power failure
- For hazardous, e.g. machinery, power tools
- Nominal plate dimensions: 86 x 86 mm
- Brushed stainless steel

**General characteristics****Synergy™ - British standard RCD sockets - Authentic**

- Slim front plate:
  - BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
  - PSS: Plates made of Stainless Steel + rust resistance
  - GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

**Documentation****Catalogue pages & additional information**

- [Description page \(p.588\)](#)

**Installation instructions & related documents**

- [LE08955AA](#)