



CLASSE300X

Simple for everyone. Perfect for you.

#ImprovingLives

bticino


A brand of **legrand**

BTICINO, A GLOBAL REFERENCE IN VIDEO DOOR ENTRY SYSTEMS, DESIGNS AND MANUFACTURES THE MOST INNOVATIVE SOLUTIONS AT ITS SITE IN ERBA (ITALY), THE LEGRAND GROUP'S ELECTRONICS CENTRE OF EXCELLENCE.

Each product is the result of extensive research combining cutting-edge technology and Italian style, an authentic expression of design and superior quality.

From concept to finished product, all the most technologically advanced solutions come to life in Italy, where quality, innovation, and craftsmanship merge in a proprietary production chain, a symbol of Italian know-how excellence. A distinctive value fully expressed in the new Classe 300X.





Contents

Classe 300X

- 4. Design
- 6. Concept
- 8. Interaction simplicity
- 10. The technology
- 12. Finishes
- 14. Sustainability
- 16. Home + Security App

Technical features

- 18. Installation
- 20. Configuration
- 22. Installation situations
- 24. Connections and functions
- 25. Main features

Catalogue and dimensional data

- 26 - 30 Catalogue
- 31. Dimensional data
- 32. Online Tools
- 33. Complete your system

Classe 300X

Attractive and
captivating design



Classe 300X stands out for its refined finishes and striking visual impact, in line with contemporary living requirements. Premium materials and minimalist lines merge in a captivating design that decorates and innovates, integrating perfectly into any modern and high-end residential environment.

Discover the harmony between form and function, for a simply elevated and intuitive user experience.



Minimal design, great innovation

The clean, monolithic design of Classe 300X further enhances the simplified user experience, discreetly integrating technology into the home environment. This philosophy reflects BTicino's approach of merging aesthetics and technology, concealing technical complexity in favour of a smooth and intuitive user experience.



7-inch touch screen display, all-glass, for a superior viewing experience and elegant design.

Only 19 mm thick and screen-to-surface ratio at the top end of the market.

Illuminated symbols and visual cues guide interaction intuitively.

Classe 300X

One smart concept,
just two keys.



The new Classe 300X video internal unit has been designed to offer unprecedented interaction simplicity, redefining the user experience in the residential video door entry system sector.



Rationality at its peak.

Inclusive design, intuitive technology, simple gestures. This is how BTicino has redefined the user experience.

At the heart of this innovation is a new intuitive graphical interface that, combined with just **two physical commands**, guarantees simple, immediate and safe interaction. These two physical commands are dedicated to the main functions of answering the call and opening the door, making operation accessible to all users. All other functions, including customisations, can be managed digitally via the touch screen display.




User notifications with bright, multi-coloured and flashing feedback

Classe 300X

Unprecedented
interaction simplicity






Even faster access to content

The device homepage automatically adapts to the configuration of the system, offering a customised and modular user experience. This “modular user experience” facilitates and simplifies navigation and enables faster access to the user's preferred content and functions. Extreme simplification of controls is key to enhancing system accessibility and safety.


Simple yet advanced interface


The Classe 300X screen graphics are designed to make daily home management easier through a modern, clear, and intuitive interface. All the main functions - such as seeing who is at the door, opening the gate, switching on the lights or receiving notifications - are always at your fingertips. The user experience is smooth, with well-organized visual commands and a design that adapts to the habits of the whole family. **Smart technology, designed to be truly simple and straightforward for everyone.**



Classe 300X

Advanced technology
accessible to everyone






Classe 300X: designed to be simple and straightforward for anyone.


The Classe 300X video internal unit integrates a 7" touch screen display with 1024 x 600 resolution for sharp, high-quality images. Thanks to the integrated digital echo canceller, audio is crystal clear and free of interference. The dual-band Wi-Fi 6 (2.4 GHz and 5 GHz) connectivity ensures even faster and more stable remote control, fully integrated with the BTicino Home+Security App.




7" touch screen display
resolution 1024 x 600 pixel



Integrated digital echo canceller



2 wires connection and Wi-Fi 6 connectivity



Home + Security App

Classe 300X

Dark
finish



Essential design, absolute elegance.

The Dark finish enhances the refined lines of the Classe 300X, with a full screen glass surface that provides an immersive and contemporary visual experience. A perfect balance of technology and style for every modern environment.




Classe 300X

Light
finish



Classe 300X in Light finish **exhibits an understated and homely elegance.**

More traditional than the Dark version, the white look fits naturally in domestic environments, conveying a sense of continuity, tradition and reassuring familiarity.

A photograph of a person's hands resting on the trunk of a large tree in a forest. The tree trunk is dark brown with a rough, textured bark. The background is a soft-focus green forest with sunlight filtering through the leaves. The text is overlaid on the left side of the image.

Classe 300X

Every detail speaks sustainability

Every material, every component and every detail stem from a precise idea: reduce environmental impact and enhance value. It's not just efficiency; it's a new concept of responsibility where every improvement, even technical, is a step toward a sustainable future.

**Materials that are reborn:
glass and recycled plastic.**

The shell is designed to last and to be environmentally friendly.

Dark version: made from more than **80% mechanically recycled plastic**, to give new life to existing materials.

Light version: **more than 25% chemically recycled plastic**, a choice that allows high technical performance but with less environmental impact.

Glass: a recyclable material, synonymous of transparency and quality.



**Zero plastic, all substance:
100% plastic-free and
FSC-certified packaging.**

Packaging made from paper and cardboard.

100% plastic-free.

FSC mix certification, guaranteeing a responsible supply chain and sourcing from sustainably managed forests.



**Efficiency that puts less strain
on the environment: reduced
consumption and lighter components.**

A more efficient design even in invisible moments:

-31% stand-by consumption compared to the previous model. Silent saving that reduces waste and environmental costs.

CO₂ under control.

A life cycle designed to put less strain on the environment:

-33% CO₂ emissions compared to the previous model. Result achieved through lower consumption, lighter electronic components and display, and the use of recycled materials.

>80%
of recycled plastic
in the Dark version

100%
plastic-free
packaging

-31%
consumption
in stand-by*

-33%
of CO₂*
emissions

(*) compared to the previous Classe 300X model.

Classe 300X

Always watchful with the Home + Security App



The best App for a safe home.

Whether you are at home or away, our App alerts you immediately if someone rings on the door, detects suspicious movements and allows you to activate the door locks with a gesture.

A simple, clear design to offer you what really matters: peace of mind.




Home + Security






- Warnings and notifications on incoming calls,
- remote activation of electrical door locks,
- timeline of past events,
- manage up to 20 homes with one account,
- a simple and intuitive interface.




Incoming call
Receive notification when someone is calling



See who's calling
answer the call and open the gate for the courier



Check the events
Check who called you and if they left you a message




Quick actions

- Activate the electrical door locks
- Activate the timed staircase lights
- Call home / Intercom
- Activate the cameras
- Manage the video door entry answering machine

Classe 300X

Installation




Same installation rules as for the 2 wires video internal units

Classe 300X stands out for its **extraordinary simplicity and quick installation**. It is a versatile solution that requires **only 2 non-polarised wires** for connection, making installation easy and foolproof.

Simply install the unit, connect the two BUS wires, and configure the main system parameters

(such as SCS addresses for the entrance panel and the internal unit).

No additional complex work is required.



For the end user

Management is autonomous and intuitive:



all configurations of the Wi-Fi network and the Home + Security App can be managed by the customer, who will be guided by clear information on the video door entry system display and in the menu of the Home + Security App.



Wall mounted and tabletop installation

Wall mounted installation using the bracket supplied with no need of masonry works.
Table-top installation possible with accessory stand (344632), to be purchased separately.

Classe 300X Configuration



Set the operating mode. Depending on the value entered a function will be implemented and one or more specific icons will appear in the Camera and Favourites sections of the home page



Defines the address of the entrance panel where the door lock release will be activated and the auto switch-on of the camera.



Device address in the video door entry system.



Classe 300X must be configured for proper operation. The configuration can be completed in two ways:

- by physically inserting the configurators into the appropriate sockets on the back of the video internal unit.
- or in advanced mode (directly from the touch screen), via the configuration section and screens on the device.

In "Physical Configuration" mode, objects are added in the camera and favourites sections.

It is not possible to add additional objects but only to customise the name of those created automatically.




Warning: device configuration performed via physical configurators CANNOT BE MODIFIED FROM THE MENU

Immediate and easy to pair with the Home + Security App

Once installed and configured, Classe 300X is ready for pairing with the **Home + Security App** (available for Android and iOS). Thanks to the Classe 300X Wi-Fi connectivity, the App allows remote management of main video door entry system functions such as receiving calls, activating electric locks, entrance panel activation, camera scrolling, updating the firmware, and managing additional activations.


Pairing is simple and straightforward, **It only takes a few simple guided steps to link the App with the video door entry system.**




Connection to the dedicated cloud automatically configures the home network safely, without router intervention. The video door entry system transfers all the parameters of the 2 wires video door entry system to the App, including cameras, door locks and activations. Using the smartphone and the App, it is possible to view the associated mobile devices and choose to disconnect or remove them at any time.

For the villa

and for one or two-family context



Installer info




- Built-in connectivity for constant connection with the home.
- Complete the system with Netatmo security solutions: outdoor and indoor cameras, alarms, smoke detectors, for a simple, smart and complete protection of the home.
- One single App (Home + Security) for the video door entry functions and the security of the home.
- The work of the installer does not change; more user-friendliness for the end user

For the apartment building or multifamily context



i Real Estate and installer info



- Preparation of the single apartment system for future expansions using Netatmo security solutions. Leaving to the end user the freedom to customise their home even at a later date.
- One single App (Home + Security) for the video door entry functions and the security of the home.
- Flexible solution, suitable for every context and adaptable to every customer.


Warning: In multi-family systems (condominium settings), it is possible to install up to 10 Classe 300X video internal units without additional power supply. For installations with more than 10 internal units, an additional 346020 power supply is required for each Classe 300X.

(*) Note: for the sizing of multi-family systems refer to the General Rules for Installation of the 2 Wires System Technical Guide

Classe 300X


Connections and functions

Front view



- 1 - Wi-Fi signal indication
- 2 - Time indication
- 3 - 7-inch touch screen display
- 4 - Favourites menu
- 5 - Professional studio (office) (ON = Enabled)
- 6 - Ringtone (🔔 = Enabled) (🔕 = Disabled)
- 7 - Settings menu
- 8 - Physical key for door lock activation
- 9 - Microphone
- 10 - Physical key for audio communication activation/deactivation
- 11 - Multicolour LED that indicates the operating status
- 12 - Notification area
- 13 - Camera area

Rear view



- 14 - Speaker
- 15 - USB-C for firmware update
- 16 - Clamps (⚡) for the connection of a call to the floor pushbutton
- 17 - 2 Wires SCS/BUS clamps
- 18 - Additional power supply clamps (1 - 2)
- 19 - Additional ringtone connection clamps (5M- 1)
- 20 - Table-top base fastening position (334632)
- 21 - ON/OFF micro-switch to enable the additional power supply
- 22 - Configurator socket (N - P - M)
- 23 - Line termination ON/OFF micro-switch
- 24 - ON/OFF micro-switch for "safe door lock" function
- 25 - Master/Slave micro-switch

Classe 300X

Main features and functions



344743



344742



MAIN FEATURES

- 7" touch screen colour LCD display
- Hands-free communication
- Dark and Light finishes
- Wall mounted installation using the supplied bracket
- Table-mounted installation with accessory base (344632)
- Available in Kit - (363942 - 363943)

AVAILABLE FUNCTIONS FROM VIDEO INTERNAL UNIT

- Activation of the electrical door lock
- Staircase light activation
- Entrance panel/scrolling activation
- Intercom
- Floor call
- Professional studio (customisable)
- Video door entry answering machine
- Master / Slave
- Safe door lock
- Wi-Fi connectivity
- Notification management
- Quick link - favourite / most used functions
- Favourite control
- 15 available ringtones

AVAILABLE FUNCTIONS FROM HOME + SECURITY APP

- Answer a video door entry system call
- Activation of the electrical door lock
- Entrance panel/scrolling activation
- Staircase light activation
- Activation and monitoring of the smart Netatmo cameras
- Management of the Netatmo Security devices (smoke sensor, burglar-alarm siren, opening sensor...)
- Video door entry answering machine
- Intercom call from smartphone to video internal unit
- History of the events

Catalogue

Classe 300X



344742



344743



344632



346020

Item	Classe 300X video internal unit - Light finish
344742	<p>2 wires/Wi-Fi hands-free connected video internal unit, Light finish, with 7" horizontal touch screen LCD display, resolution 1024 x 600 pixel. Featuring two physical keys for answering/ending calls, entrance panel activation, and controlling the electric door lock.</p> <p>The remaining video door entry system functions e.g. entrance panel activation, camera scrolling, additional door lock activation, video door entry system answering machine, staircase light control, intercom etc. are managed via specific menus and touch display.</p> <p>Featuring a digital echo canceller for better audio quality. LED visual signals for: Wi-Fi network connection status, info / notifications and call exclusion. Using the touch display, it is possible to access the notification list, as well as your favourite door entry controls. Advanced 'Professional Studio' and 'Do Not Disturb' functions: customisable and schedulable by day/time. Possibility of voice communication with the switchboard - if present in the system - after a specific call.</p> <p>The device must be configured by physically connecting the configurators, or using the menu and the touch display, which will give better possibilities of customisation of associated functions and texts.</p> <p>Thanks to the Wi-Fi 6 connectivity, the video door entry system can connect to 5 GHz or 2.4 GHz band routers to take advantage of the functions available on the Home + Security App (available for Android and iOS): call reception, door lock release, event timeline display, entrance panel activation, camera scrolling and advanced «Professional Studio» and «Do Not Disturb» functions.</p> <p>Using the Home + Security App, it is also possible to manage products from Netatmo security offering. 15 different ringtones available.</p> <p>Wall mounted installation using the bracket supplied and tabletop installation (with support 344632) to be purchased separately.</p> <p>Made with over 25% chemically recycled plastic. Designed, engineered, and manufactured in Italy.</p>

Item	Classe 300X video internal unit - Dark finish
344743	As the video internal unit 344742 but with Dark finish. Made with over 80% mechanically recycled plastic.
344632	Tabletop support for Video internal unit Accessory support for the tabletop installation of the Classe 300X video internal units (344742 – 344743).
346020	2 DIN additional power supply Additional 2 DIN power supply to be used to supply Classe 300X video internal units locally using the clamps (1 – 2).



Kit solutions with Classe 300X



363942



363943

Practical and comprehensive kit solutions simplify installation and ensure maximum system compatibility and expandability. By purchasing a single item code, the kit case contains all the necessary materials, together with detailed technical instructions for installation, connection, start-up and expansion of the system.

The new kit solutions with Classe 300X and Linea 3000 outdoor pushbutton panel offer an optimised video experience, thanks to the 7-inch touch display with 1024x600 pixel resolution and the camera integrated in the Linea 3000 pushbutton panel, now further improved.

The result is a sharper and more detailed view.



Catalogue

Linea 3000 - Classe 300X kit



 H + S

363942



 H + S

363943

Item	Kit with Linea 3000 Black finish with RFID key card and Classe 300X Light finish
363942	<p>One-family hands-free kit with Classe 300X hands-free connected video internal unit (Light finish) and Linea 3000 pushbutton panel (black finish).</p> <p>2 wires/Wi-Fi hands-free connected video internal unit, Light finish, with 7" horizontal touch screen LCD display, resolution 1024 x 600 pixel.</p> <p>Featuring a digital echo canceller for better audio quality. Thanks to the Wi-Fi 6 connectivity, the video door entry system can connect to 5 GHz or 2.4 GHz band routers to take advantage of the functions available on the Home + Security App (available for Android and iOS): call reception, door lock release, event timeline display, entrance panel activation, camera scrolling and advanced «Professional Studio» and «Do Not Disturb» functions. Through the Home + Security App, it is also possible to manage the products of the Netatmo security range (outdoor and indoor cameras, door and window sensors, indoor siren and smoke detector).</p> <p>This allows you to quickly and easily create a Smart security system. Linea 3000 pushbutton panel with black finish zamak front cover and proximity reader with a kit of coloured RFID key cards and two clear discs for door lock release. Can be wall or flush installed with specific accessories: (350020) flush mounted box and (343063) flush mounted accessory - to be purchased separately. Can be fitted with rainshield (343053) - to be purchased separately. The pushbutton panel has a protection index IP54 - protection index against mechanical impact IK10.</p>

Item	Kit with Linea 3000 Black finish with RFID key card and Classe 300X Dark finish
363943	<p>One-family hands-free kit with Classe 300X hands-free connected video internal unit (Dark finish) and Linea 3000 pushbutton panel (black finish).</p> <p>2 wires/Wi-Fi hands-free connected video internal unit, Dark finish, with 7" horizontal touch screen LCD display, resolution 1024 x 600 pixel.</p> <p>Featuring a digital echo canceller for better audio quality. Thanks to the Wi-Fi 6 connectivity, the video door entry system can connect to 5 GHz or 2.4 GHz band routers to take advantage of the functions available on the Home + Security App (available for Android and iOS): call reception, door lock release, event timeline display, entrance panel activation, camera scrolling and advanced «Professional Studio» and «Do Not Disturb» functions. Through the Home + Security App, it is also possible to manage the products of the Netatmo security range (outdoor and indoor cameras, door and window sensors, indoor siren and smoke detector).</p> <p>This allows you to quickly and easily create a Smart security system. Linea 3000 pushbutton panel with black finish zamak front cover and proximity reader with a kit of coloured RFID key cards and two clear discs for door lock release. Can be wall or flush installed with specific accessories: (350020) flush mounted box and (343063) flush mounted accessory - to be purchased separately. Can be fitted with rainshield (343053) - to be purchased separately. The pushbutton panel has a protection index IP54- protection index against mechanical impact IK10.</p>

Item	Kit composition	Q.ty
343093	Linea 3000 pushbutton panel with Black Zamak finish	1
344742	Classe 300X video internal unit with Light finish	1
346050	6 DIN power supply	1
346250	Door lock relay accessory	1
346260	Set of coloured door lock release key cards	1
	Set of door lock release clear discs	1

Item	Kit composition	Q.ty
343093	Linea 3000 pushbutton panel with Black Zamak finish	1
344743	Classe 300X video internal unit with Dark finish	1
346050	6 DIN power supply	1
346250	Door lock relay accessory	1
346260	Set of coloured door lock release key cards	1
	Set of door lock release clear discs	1




Item Smart Original outdoor cameras

- 392050 Original outdoor camera**
 The Intelligent Outdoor Security Camera offers advanced detection of people, animals and vehicles. It features a robust monobloc aluminium structure with a white finish and is made of ultra-resistant UV-protected glass and plastic materials. The 5 MP video sensor and 2K resolution enable H.264 encoding, ensuring efficient streaming and storage. The camera provides long-distance detection up to 20 metres, with a wide viewing angle of 130° and 16x digital zoom for detailed video analysis. An integrated microphone allows real-time audio monitoring, while the 12 W LED spotlight offers adjustable brightness for optimal visibility. Infrared night vision ensures clear images even in low light up to 15 meters. Access to the camera is protected by end-to-end encryption thanks to the Home + Security App. Designed specifically for outdoor use, the device is weatherproof and benefits from HZO protection for increased durability. Connectivity is provided by dual-band Wi-Fi, compatible with both 2.4 GHz and 5 GHz frequencies.
- 392051** As 392050 but with black finish.
- 392060 Original outdoor camera with PoE**
 The intelligent outdoor security camera combines high-performance technology and refined design, providing reliable surveillance in any environment. The monobloc aluminium body with white finish ensures exceptional durability, while the ultra-resistant glass and plastic components offer robust UV protection. Equipped with a 5 MP video sensor and 2K resolution (≈ 2560 × 1440), the camera delivers sharp, detailed images. Long-distance detection – up to 20 m – enables precise identification of people, animals, and vehicles, supported by a 130° field of view and 16x digital zoom. The integrated microphone allows real-time audio monitoring, while the integrated LED spotlight (12 W) with adjustable intensity improves visibility. Infrared night vision extends up to 15 m, ensuring reliable performance even in total darkness. Access is encrypted and safely managed through the Home + Security App. Designed for outdoor use, the camera features HZO waterproof protection and connects via Power over Ethernet (PoE).
- 392061** As 392060 but with black finish.

Item Smart Advance indoor cameras

- 391950 Advance indoor camera**
 Advance indoor camera with facial recognition optimised by artificial intelligence (AI). Smart shutter for privacy and filming only of strangers. Wi-Fi connection. Access to images live via smartphone and the Home + Security App. It can be combined with the indoor siren item NIS01-PRO to create a customised alarm system. Compatible with Alexa, Apple Homekit and Google Assistant. Adjustable monobloc body in painted aluminium. White colour.
- 391951** As 391950 but with black finish.
- 391952 Advance indoor camera**
 Indoor camera 391950 + accessory for installation with 3-module box with depth of at least 40 mm or BTicino 503E and PB503N boxes - white colour.
- 391953** As 391952 but with black finish.
- 391954 PoE adapters**
 PoE adapter to exclusively power and connect 391950/51 indoor cameras using a single cable to ensure a reliable and stable wired connection. White colour.
- 391955** As 391954 but with black finish.
- 391956 Mounting accessories in 2-module boxes**
 Accessory for installing the Advance indoor camera on a 2-module box with at least 40 mm depth. Also compatible with the BTicino 502E and PB502N boxes - white colour.
- 391957** As 391956 but with black finish.

CAUTION: The items are expected to be available during 2026. Please check with your technical sales representative.





NIS-01-PRO



NSA-PRO-EU



NCO-PRO

Smart indoor siren

NIS-01-PRO

Smart indoor siren with 110 dB alarm, pre-recorded sounds and vibration sensor for tamper detection. Battery power supply or with a cable (not supplied) using the USB micro port. It only works with the smart indoor camera and must be installed in the same room: Bluetooth Low Energy (BLE) wireless connection with the smart indoor camera. Declaration of conformity and FCC declarations. Open-source compatibility. Operation using the Home + Security app.

Smart smoke detector

NSA-PRO-EU

Smart smoke detector with 85 dB alarm, high performance photoelectric sensor, average coverage 50 m², notifications on the smartphone through the Home + Security App

Smart carbon monoxide detector


Item

NCO-PRO

Intelligent wall-mounted carbon monoxide detector. Monitors combustion appliances (boiler, fireplace, wood stove, gas cooker, etc.) by measuring carbon monoxide levels in real time. When carbon monoxide is detected, it triggers its 85-decibel alarm and sends a real-time notification to the smartphone. Featuring a 10-year battery: the maximum lifespan for all carbon monoxide detectors. The Auto-Test function checks for correct operation. If a problem is detected, it sends a notification to the smartphone. Reliability guaranteed by CE (EN 50291) and NF certifications. Standalone device, no hub required. Compatible with Apple HomeKit. Operation using the Home + Security app. Requirements: it needs high-speed wireless internet connection. Public hotspots are not supported. The intelligent carbon monoxide alarm will detect carbon monoxide and emit a sound alarm even if the Wi-Fi is not configured. However, Wi-Fi is required to receive smartphone alerts. Wi-Fi 802.11 b/g/n (2.4 GHz), Open/WEP/ WPA/ WPA2-Personal, Bluetooth Low Energy (BLE)



Dimensional data



Classe 300X

LEGAL NOTES

In order to use the video door entry system call forwarding service on smartphones, the customer must have the necessary technical equipment to access the Internet network, through a contract with an Internet Service Provider (ISP).

BTicino assumes no responsibility and is not involved in agreements between the customer and the ISP.


Access to some additional BTicino services, beyond the basic Classe 300X video door entry system functions, requires the installation of the Home+Security App on the customer's mobile device.

These services allow remote interaction with the video door entry system via Internet connection.

Proper operation of the integration between video door entry system and App depends on Wi-Fi signal quality, the type of home Internet contract, and the smartphone data plan. If any of these factors do not meet the necessary technical requirements, BTicino accepts no liability for any malfunctions or failures.

It should also be noted that the product supports a streaming VoIP system, so it is essential to check that the data contract signed does not prevent its use. Please also note that the use of the remote service via the App involves data consumption, the cost of which is the responsibility of the customer and depends on the contractual conditions with the ISP.

Online design, budgeting and customisation tools



YouDiagram

Software for the design and budgeting of BTicino audio and video door entry systems (2 wires, IP, 8 wires, analogue).

It gives the possibility of creating a single line diagram of the system, which can then be exported in PDF and DXF format, of selecting the products and their finishes, of configuring the devices and checking current consumptions.

It can be downloaded from: <https://www.bticino.com/tools/design-software/youdiagram>



Video door entry system Configurator

Web app for the configuration and budgeting of audio and video door entry systems for villas and apartment blocks.

What it allows to do:

- 1. System creation**, depending on the type of system and the characteristics of the property
- 2. Get an estimate.** At the end of the configuration, a detailed and complete list of materials is generated.
- 3. Access the project at any time.**

Access the restricted area to view or modify the project.

Accessible from: <https://www.bticino.com/tools/web-applications-for-configuration-and-quotation/video-door-entry-system-configurator>



WORLD PRESENCE

LEGRAND OPERATES ON A GLOBAL MARKET, WITH FACILITIES IN NEARLY 90 COUNTRIES AND PRODUCTS SOLD IN NEARLY 180.

Together, the Group's expertise, the scope of its offering adapted to local markets as well as its international presence make Legrand a worldwide benchmark.

Video door entry system

System solutions for Bticino entrance panels

Complete your system with the outdoor pushbutton panel of your choice.



LINEA 5000

Ideal for the “digitalisation” of multi-family settings, it takes access to modern buildings to the next level.

Featuring a large 7” touch screen display, a wide angle high-quality camera, digital filters and a modern and intuitive graphic interface, it integrates perfectly with contemporary buildings..



LINEA 3000

Specifically conceived **for villas and single-family houses**, Linea 3000 is a stylish, robust pushbutton panel. This solution, even more refined thanks to the Zamak (grey or black finish), flawlessly combines technological innovation and design.



SFERA

Sfera New and Sfera Robur pushbutton panels are characterised by outstanding design, style, sturdiness, and a complete range of functions.

They are available in two versions. The electronic modules are compatible with both versions, allowing maximum simplification of goods in the warehouse.



Classe 300X

Simple for everyone.
Perfect for you.



BTicino SpA
Viale Borri, 231
21100 Varese - Italy
www.bticino.com

bticino
A brand of  **legrand**

AD-EXCM300X/26C/ENG - 02/2026

In accordance with its continuous improvement policy, the Company reserves the right to change specifications and designs without prior notice.
All illustrations, descriptions, dimensions and information appearing in the catalogue are indicative and cannot be considered binding for the Company.